


Soft Close Instructions

Step One:




Above shows how your door will arrive, with the soft close mechanism pre-assembled to your doors. Above shows a left hand soft close.

Step Two:



To find the measurement so that you can fit the activator in the top track, measure from the front edge of your door to the front edge of the soft close add on 55mm.

Step Three:



If your measurement from the edge of your door to the start of the soft close was 250mm (Step Two) then the activator should be fitted into the top track $250 + 55\text{mm} = 305\text{mm}$. The activator is fitted from the edge of the activator at 305mm.

Step Four:

Adjust your door height until the soft close catches the activator in the top track.